



## Abrasive flap disc speed ZA, flat, Ø 115 mm, Grit: 40



### Order data

|              |               |
|--------------|---------------|
| Order number | 565294 40     |
| GTIN         | 4062406159573 |
| Item class   | 52M           |

### Description

#### Version:

- High-quality zirconium aluminium oxide (ZA) for high abrasive performance.
- Glass fibre pad for optimum contact pressure.
- Suitable for both steel and stainless steel.
- Best results on angle grinders of all power classes.

**speed** - flat flap strip arrangement, for **high metal removal rate** and long tool life.

#### Application:

Precise chamfering, edge smoothing and surface abrasion.

### Technical description

|                      |                         |
|----------------------|-------------------------|
| Disc Ø               | 115 mm                  |
| Shape description    | flat                    |
| Bore Ø               | 22.23 mm                |
| Grinding media       | Zirconium abrasive (ZA) |
| Grinding medium code | ZA                      |

|   |                    |
|---|--------------------|
| Iron, sulphur and chlorine constituents | < 0.1 %            |
| Product name attribute                  | Ø 115 mm           |
| optimised for material                  | INOX               |
| optimised for material                  | Steel              |
| maximum circumferential speed           | 80 m/s             |
| Type of product                         | Abrasive flap disc |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable                                  |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable only under restricted conditions |                |          |
| Uni                            | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |