




Pitbull clamp blunt edge, Thread M: M10



Order data

Order number	370030 M10
GTIN	4046368563753
Item class	37M

Description

Version:

- **Clamp with socket-head screw to DIN912, with oil-tight O-ring.**
- **Secure and precise clamping.**
- **Compact size, so few interference contours.**

Blunt edge for general tasks.

Application:

Ideal for multiple clamping.

Technical description

Clamping travel	1.7 mm
Clamping width	25.4 mm
Height H ₂	6.3 mm
Thread M	M10
Clamping force	26 kN
H	18.03 mm

Material	Steel
H ₁	11.4 mm
B ₁	10.2 mm
B _{H9}	25.4 mm
maximum tightening torque	40 Nm
Type of product	Jig clamping system