

HOLEX

Solid carbide high performance drill, Whistle-Notch shank DIN 6535 HE, TiN, Ø DC h7: 17mm



Order data

Order number	122355 17
GTIN	4045197394231
Item class	12E

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

NEW GENERATION AVAILABLE!

Recommended successor product is No. 122508.

Technical description

Flute length L_c	73 mm
Shank tolerance	h6
Feed f in steel $< 900 \text{ N/mm}^2$	0.28 mm/rev.
Number of cutting edges Z	2
Nominal $\varnothing D_c$	17 mm
Tolerance nominal \varnothing	h7
Shank $\varnothing D_s$	18 mm
Overall length L	123 mm
Standard	DIN 6537 K
recommended maximum drilling depth L_2	47.5 mm

Coating	TiN
Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HE to h6
Through-coolant	yes, with 25 bar
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm ²	suitable	110 m/min	P
Steel < 750 N/mm ²	suitable	90 m/min	P
Steel < 900 N/mm ²	suitable	80 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	65 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	35 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable	30 m/min	M
Ti > 850 N/mm ²	suitable	30 m/min	S
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable only under restricted conditions		