

**Cutting disc Silver, Disc Ø: 125mm****Order data**

Order number	563325 125
GTIN	5902658104978
Item class	53M

Description**Version:**

Silver cutting discs with high cutting speeds and long working life. Grit mixture with **precision-shaped ceramic grit**.

Application:

For fast, low-burr cutting with low thermal stress.

Specification:

A36R-BF.

Technical description

Disc Ø	125 mm
Disc thickness	1 mm
Bore Ø	22.23 mm
Shape description	flat
Series	SILVER
for material thicknesses	3 - 5 mm

Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
recommended approach angle	90 degrees
optimised for material	Steel
optimised for material	HSS
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		