

Garant GRIDLINE

CNC cabinet complete with tool sockets, with roller shutter, for tool shanks: HSK50**Order data**

Order number	971309 HSK50
GTIN	4062406164362
Item class	9GI

Description**Version:**

Equipped cabinet in 40×20G. With mounting rails adjustable in 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** with 4 individually adjustable feet to compensate for unevenness in the floor. Maximum **load capacity per mounting rail pair 200 kg, per tool block insert rail 150 kg.**

Roller shutter of anodised aluminium profiles, colour not configurable.

Supplied with:

Cabinet including mounting rails No. 971525 size 20 and shelves with tool sockets No. 971570.

Colour:

Body, mounting rails and shelves RAL 7035 light grey, **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width in G	40
Depth in G	20
Axial spacing A	71 mm
Width	1000 mm
Weight	146 kg
Depth	500 mm
Number of tool sockets	189
Height	2000 mm
Number of tool block insert rails	9
Mounting rails	9 pair
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Cabinet fronts	Roller shutter
Type of product	CNC cabinet

Accessories

Shelf with tool sockets for cabinet / compartment width 40 G for tool shanks HSK50	971570 HSK50
Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 20	971525 20
Plastic insert Type HSK50	947390 HSK50