



Cordless impact wrench / driver, Type: 71150464



Order data

Order number	074000 71150464
GTIN	4014586887388
Item class	03F

Description

Version:

Robust and **powerful cordless impact wrench / driver** with durable **metal gearbox**, all-metal impact drive and ergonomic **central handle with soft-grip coating**.

Stage of charge display, LED illumination of the working area. Reversible, with electronic speed control. 10% higher torque in reverse. Electronic torque adjustment in 6 steps.

Select Version.

- **3/8 inch square drive socket.**
- **135 Nm maximum torque.**

Advantage:

Electronic torque adjustment in 6 steps.

Supplied with:

Without battery and without charger, with carrying case.

Note:

For matching spare batteries and accessories see No. 073835, battery starter sets can be found under No. 073832.

Technical description

Tool arbor drive profile	External square drive
Number of impacts	0 - 3600 min ⁻¹
maximum torque	135 N·m
maximum vibration to EN	14.5 m/s ²
Weight	0.85 kg
typical application	Strong
Tool arbor size	3/8 in
Manufacturer's designation	ASCD 12-150 W8
Battery voltage	12 V
maximum screw Ø (8.8 - 12.9)	M14
suitable battery - supplier / battery type / voltage	Fein type E 12 V
Packaging	Carrying case
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Li-ion battery Rechargeable battery type, battery voltage FE12 V	073835 FE12
Li-ion battery Rechargeable battery type, battery voltage FE12 V	073837 FE12