

Garant GRIDLINE

**CNC cabinet complete with tool sockets, with roller shutter, for tool shanks:
VDI40****Order data**

| | |
|--------------|---------------|
| Order number | 971349 VDI40 |
| GTIN | 4062406164751 |
| Item class | 9GI |

Description**Version:**

Equipped cabinet in 40×20G. With mounting rails adjustable in 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** with 4 individually adjustable feet to compensate for unevenness in the floor. Maximum **load capacity per mounting rail pair 200 kg, per tool block insert rail 150 kg.**

Roller shutter of anodised aluminium profiles, colour not configurable.

Supplied with:

Cabinet including mounting rails No. 971525 size 20 and shelves with tool sockets No. 971570.

Colour:

Body, mounting rails and shelves RAL 7035 light grey, **powder-coated.**

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|----------------------------------------|----------------------------------------------------------------|
| Number of tool sockets | 102 |
| Weight | 126 kg |
| Width | 1000 mm |
| Axial spacing A | 75 mm |
| Depth | 500 mm |
| Height | 2000 mm |
| Depth in G | 20 |
| Width in G | 40 |
| Mounting rails | 2 pair |
| Number of tool block insert rails | 6 |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1000 kg |
| Height adjustment interval | 25 mm |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Cabinet fronts | Roller shutter |
| Type of product | CNC cabinet |

Accessories

| | |
|---------------------------------------------------------------------------------------|--------------|
| Mounting rails for shelves with tool sockets, pair suitable for cabinet depth in G 20 | 971525 20 |
| Shelf with tool sockets for cabinet / compartment width 40 G for tool shanks VDI40 | 971570 VDI40 |
| Plastic insert Type VDI40 | 947390 VDI40 |