

Garant GRIDLINE

mLevel workstation with ESD coating, Length: 1500mm**Order data**

Order number	972010 1500
GTIN	4062406167011
Item class	9GW

Description**Version:**

mLevel workstation, ESD conductive according to DIN EN 61340-5-1, the work place which adapts to your needs. Classic, manual height adjustment in 25 mm intervals using a support leg with securing bolts. Scaling on the inner surface of the table showing the exact working height for ease of operation. **All-round 3 mm antistatic ABS edge band**. Central grounding point underneath the worktop. The support legs are not used for earthing. **With internal steel tube as reinforcement profile**

Colour:

Light grey similar to RAL 7035 **ESD powder-coated**.

Note:

All plastic components (e.g. covering caps) are not ESD conductive.

Technical description

Worktop depth	700 mm
Worktop length	1500 mm
Weight	70 kg
Series	Workstation
Worktop thickness	40 mm
Height adjustment range (worktop surface) from – to	750 - 1000 mm

Coating thickness	0.8 mm
Stepless height adjustment	no
Model	mLevel
Width	1500 mm
Control panel with display and memory functions	no
Colour of worktop surface	light grey RAL 7035
Principle of height adjustment	complete structure
Worktop covering	HPL plastic, conductive
Depth	800 mm
Material of worktop	ESD worktop
Height adjustment workstation	750-1000 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	mechanical
Insert thickness	40 mm
Height adjustment	25 mm
electrostatic characteristic	EGB/ESD
Type of product	Work table