

Garant GRIDLINE

**eLevel workstation with ESD coating, Length: 2000mm****Order data**

Order number	972013 2000
GTIN	4062406167059
Item class	9GW

**Description****Version:**

**eLevel workstation, ESD conductive according to DIN EN 61340-5-1.** With continuous electrical adjustment for height. Height adjustment by pushbutton. Push-button adjustment to find a suitable **height for the entire workstation. All-round 3 mm antistatic ABS edge band.** Central grounding point underneath the ESD worktop. The support legs are not used for earthing. **With internal steel tube as reinforcement profile**

**Colour:**

Light grey similar to RAL 7035 **ESD powder-coated.**

**Note:**

All plastic components (e.g. covering caps) are not ESD conductive.

- **If using casings attached to the underside of the worktop, note that such casings may not exceed a maximum height of 500 mm.**
- **Caution: when installing benches in a row, please use side plates no. 972019 (crush hazard).**

**Technical description**

Stepless height adjustment	yes
Series	Workstation
Worktop depth	700 mm
Colour of worktop surface	light grey RAL 7035

Principle of height adjustment	complete structure
Coating thickness	0.8 mm
Worktop thickness	40 mm
Model	eLevel
Depth	800 mm
Weight	93 kg
Material of worktop	ESD worktop
Worktop covering	HPL plastic, conductive
Height adjustment range (worktop surface) from – to	670 - 990 mm
Control panel with display and memory functions	yes
Worktop length	2000 mm
Width	2000 mm
Nominal voltage	250 V
Plug type, input	F
Height adjustment workstation	670-990 mm
Design version	Steel hollow section construction
Workbench/desk load capacity - maximum distributed load (on wood)	250 kg
Type of height adjustment	electrical
Insert thickness	40 mm
Height adjustment	25 mm
electrostatic characteristic	EGB/ESD
Type of product	Work table