

Garant**Transport trolley with solid rubber wheels, Usable width mm / model: 627/B****Order data**

Order number	970016 627/B
GTIN	4062406163181
Item class	91L

Description**Version:**

Sturdy chassis with 2 ball-bearing fixed wheels and 2 castors (with parking brake) (Ø 160 mm). The stiles are positively fitted to the chassis and the push handle, and bolted to them. Side panels are perforated with a 25 mm grid to accept carrier rails and tool carriers.

Supplied with:

Tool trolley with 2 side panels, with push handle and solid rubber wheels.

Colour:

Body RAL 7035 light grey, side walls RAL 7016 anthracite grey **powder-coated**.

Note:

Suitable carrier rails for GARANT Tool UNIT toolholders can be found under No. 970110, GARANT Tool UNIT under No. 971000. Suitable tool carriers can be found under No. 970125 or No. 970130.

Technical description

Number of fixed wheels without parking brake	2
Depth	1100 mm
Number of tool carriers (1 level)	7
Wheel Ø	160 mm

Width	675 mm
Usable width	627 mm
maximum load capacity	400 kg
Footprint depth	1100 mm
Height	925 mm
Material of wheel	Solid rubber
Footprint width	675 mm
Model	B
Number of carrier rails (1 level)	4
Number of castors with parking brake	2
Material thickness	1.2 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	CNC tool trolley

Accessories

Tray with cover for modular tool trolley Width 627 mm	970175 627
Tray for modular tool trolley Width 627 mm	970170 627