

Garant GRIDLINE

## ESD module for energy and media, Module type: AIR/S



### Order data

Order number	972220 AIR/S
GTIN	4062406167905
Item class	9GW

### Description

#### Version:

Of sheet metal **modular design**. All power components include **cables** and **plugs**. Plug and play insertion principle. Powered modules are pre-assembled with a connecting cable and 3-pin plug No. 928491 size 3 for direct connection to the distribution block. Module No. 928470 size CEE400/5 pre-assembled with a connecting cable and 5-pin plug No. 928491 size 5.

#### Description:

##### Technical data for industrial plug-in system (No. 928490; 928491; 928492):

- **Maximum connection value 230 V / AC, 16 A or 400 V / AC, 16 A.**
- **Total load capacity at AC: 3.5 kW.**
- **Maximum connected load, three-phase AC: 10.5 kW.**
- **Conductor cross-section of the pre-assembled cables:**
  - 3 × 1.5 mm<sup>2</sup> for single-phase AC (L, N, PE)**
  - 5 × 1.5 mm<sup>2</sup> for three-phase AC (L1, L2, L3, N, PE)**
- **Protection class 1**
- **Index of Protection IP 20.**

#### Application:

The following list shows our socket types with descriptions of the respective types of plugs. Suitability for use in the various countries can be determined by the type of plug.

Germany / DE: Type F

Switzerland / CH: Type J

Italy / IT: Type L  
 France / FR: Type E  
 Czech Republic / CZ: Type E  
 England / GB: Type G  
 Denmark / DK: Type K  
 USA / US: Type B

**Suitable for:**

No. 972200 – 972203.

**Colour:**

Light grey similar to RAL 7035 **ESD powder-coated.**

**Note:**

- **When assembling the media tracks with modules individually, check that the maximum number of module divider units is not exceeded.**
- **The articles No. 972220 size US110V/1 and US110V/2 may only be fitted in combination with the following modules: \_ON/OFF1, \_COVER, \_AIR/S, \_NET, \_USB, \_USB/5V, \_LINK.**
- **All plastic components (e.g. covering caps) are not ESD conductive.**
- **Initial connections and also the connection of plugs and sockets to cables should be performed only by a qualified electrician.**

---

**Technical description**

Divider unit	1U
Version	up to 16 bar
Description	Safety one-hand coupling; quick-release compressed air coupling, NB 7.2; connection thread 3/8 inch.
Material thickness	1.5 mm
electrostatic characteristic	EGB/ESD
Type of product	Power module