

KÄRCHER**Wet and dry vacuum cleaner, Manufacturer's designation: NT55T2ME****Order data**

| | |
|--------------|-----------------|
| Order number | 078521 NT55T2ME |
| GTIN | 4039784538092 |
| Item class | 07C |

Description**Version:**

Powerful all-purpose **wet and dry cleaners** with high suction power and compact design, hose storage, and accessory storage on the cleaner. **Automatic shut-down** when the maximum filling level is reached in the container.

- **Folded filter enables wet and dry suction without removing the filter.**
- **The Tact automatic filter cleaning system permits uninterrupted work in combination with low maintenance costs and long working life of the filter.**
- **The central rotary switch permits easy switching between the suction programs.**
- **Top-class industrial vacuum cleaner with 2 maintenance-free suction turbines and further development of the Tact² automatic filter cleaning system for continuous uninterrupted working.**
- **Outstanding suitability for removing even large quantities of fine dust right through to coarse dust and liquids.**
- **For emptying, the stainless steel tank can be completely removed from the mobility trolley and taken to a disposal point.**
- **Anti-static system (grounding up to the suction hose connection) and protection class I.**
- **Robust 55-litre container with bumpers and metal castors.**

Supplied with:

Suction hose with elbow, metal suction tube 2x0.5 m, floor nozzle, and crevice nozzle, flat fold filter or paper filter bag.

Note:

Industrial vacuum cleaner No. 078522 for materials that are oily or contain oil.

Technical description

| | |
|-----------------------------|---|
| Fine dust suitability | yes |
| Air flow volume | 2x74 l/s |
| Operating noise | 73 dB(A) |
| Manufacturer's designation | NT 55/2 Tact ² Me I |
| Power consumption | 2760 W |
| Filter cleaning | Tact ² automatic filter cleaning |
| Cable length | 10 m |
| Anti-static system | yes |
| Length | 710 mm |
| Weight | 45 kg |
| Dust class – vacuum cleaner | L |
| Width | 570 mm |
| Number of turbines | 2 |
| Vacuum | 254 mbar |
| Connection width | 40 mm |
| Height | 1070 mm |
| Container volume | 55 l |
| Suction hose length | 4 m |
| Filter system | Fan-fold filter |
| Special features | Stainless steel tank, anti-static, protection class I |
| Power supply | Mains operated |
| Type of product | Wet and dry vacuum cleaners |

Accessories

| | |
|---|-------------|
| Crevice nozzle, narrow, 13 mm Connection width DN40 | 078528 DN40 |
| Rubber oblique-end nozzle Connection width DN40 | 078527 DN40 |