

Garant GRIDLINE

## ESD media track with 4 sockets 250V, suitable for type: 1000



### Order data

Order number	972202 1000
GTIN	4062406167608
Item class	9GW

### Description

#### Version:

Of sheet metal **modular design**. All power components include **cables** and **plugs**. The modules and covers can be changed / positioned as desired.

- Cable slots are provided on the upper, lower, and end faces for power supplies and for linking multiple media tracks together.

#### Electrical pre-installation with industrial plug-in system (applies only to media tracks):

1 pc. distribution block No. 928492 with 5-pin feed/supply cable and 5 pcs. 3-pin sockets,  
1 pc. 5-pin plug connector No. 928490 size 5 included for the feed cable.

#### Description:

#### Technical data for industrial plug-in system (No. 928490; 928491; 928492):

- **Maximum connection value 230 V / AC, 16 A or 400 V / AC, 16 A.**
- **Total load capacity at AC: 3.5 kW.**
- **Maximum connected load, three-phase AC: 10.5 kW.**
- **Conductor cross-section of the pre-assembled cables:**
  - 3 × 1.5 mm<sup>2</sup> for single-phase AC (L, N, PE)**
  - 5 × 1.5 mm<sup>2</sup> for three-phase AC (L1, L2, L3, N, PE)**
- **Protection class 1**
- **Index of Protection IP 20.**

#### Suitable for:

Support columns No. 972080. Installation by **insertion**.

#### Colour:

Light grey similar to RAL 7035 **ESD powder-coated**.

#### Note:

- **All plastic components (e.g. covering caps) are not ESD conductive.**
- **Initial connections and also the connection of plugs and sockets to cables should be performed only by a qualified electrician!**

- For information on the technical data of the industrial plug-in system, see eShop [www.hoffmann-group.com](http://www.hoffmann-group.com) under the appropriate article number.

## Technical description

Installation height	160 mm
Width	920 mm
suitable for type	1000
Divider unit	8 units
Nominal voltage	250 V
On/Off switch	no
Number of sockets type F	4
Plug type, input	GST plug-in system
Socket type	F
Type of current	AC
Material thickness	1.5 mm
electrostatic characteristic	EGB/ESD
Type of product	Power module

## Accessories

ESD module for energy and media Module type DE250V/2	972220 DE250V/2
------------------------------------------------------	-----------------