

Garant GRIDLINE

ESD cabinet with shelves with plain sheet metal swing doors, Number of pull-out frames: 1000mm**Order data**

Order number	972380 1000
GTIN	4062406180720
Item class	9GI

Description**Version:**

Cabinet **ESD conductive**, to DIN EN 61340-5-1. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** with 4 individually adjustable feet to compensate for unevenness in the floor.

Performance of ESD tests based on DIN EN 61340-5-1. Measurement of the resistance to an equipotential bonding system connection point is performed using a limit value $R_{gp} < 1G\Omega$. Storage shelves are **ESD powder-coated**. The plastic feet of the cabinet are not ESD-conductive, therefore the earthing point of the cabinet must be connected to the equipotential bonding system of the building.

Colour:

Light grey similar to RAL 7035 **ESD powder-coated**.

Note:

Delivered without ESD protective packaging. All plastic components (e.g. covering caps and push handles) are non-ESD conductive.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	56 kg
Cabinet fronts	Plain sheet metal swing door
Depth	500 mm
Shelf load capacity / maximum distributed shelf load (on metal)	35 kg
Depth in G	20
Height	1000 mm
Usable height	845 mm
Width	1000 mm
ComfortClose	no
Electronic locking system can be retrofitted	yes
Width in G	40
Number of shelves	2
Handle positioning	top
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Type of product	Cabinet with shelves

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------