

Garant GRIDLINE

ESD cabinet with shelves with plain sheet metal swing doors, Number of pull-out frames: 2000mm**Order data**

Order number	972380 2000
GTIN	4062406180737
Item class	9GI

Description**Version:**

Cabinet **ESD conductive**, to DIN EN 61340-5-1. Mountings for shelves at 25 mm intervals. Swing doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock. **Levelling base** with 4 individually adjustable feet to compensate for unevenness in the floor.

Performance of ESD tests based on DIN EN 61340-5-1. Measurement of the resistance to an equipotential bonding system connection point is performed using a limit value $R_{gp} < 1G\Omega$. Storage shelves are **ESD powder-coated**. The plastic feet of the cabinet are not ESD-conductive, therefore the earthing point of the cabinet must be connected to the equipotential bonding system of the building.

Colour:

Light grey similar to RAL 7035 **ESD powder-coated**.

Note:

Delivered without ESD protective packaging. All plastic components (e.g. covering caps and push handles) are non-ESD conductive.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	500 mm
Width in G	40
Number of shelves	5
ComfortClose	no
Cabinet fronts	Plain sheet metal swing door
Width	1000 mm
Usable height	1845 mm
Weight	102 kg
Height	2000 mm
Depth in G	20
Electronic locking system can be retrofitted	yes
Handle positioning	top
Shelf load capacity / maximum distributed shelf load (on metal)	35 kg
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
electrostatic characteristic	EGB/ESD
Type of product	Cabinet with shelves

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------