

**Garant**
**eco clamping toolholder, right-hand, Shank size / insert size L: 25/16mm**

**Order data**

Order number	271993 25/16
GTIN	4062406180775
Item class	21U

**Description**
**Version:**

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability.

**Supplied with:**

**With shim 1.5°.**

**Note:**

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Through-coolant: yes

Functional width L<sub>4</sub>: 25 mm

Head length L<sub>1</sub>: 30 mm

Overall length L: 101.5 mm

Shim 1.5°: 279819 1

Shim screw: 259027 6

Clamp, screw, O-ring: 259036 15

**Technical description**

Shank size	25 mm
suitable for insert size	16 mm
Head length L <sub>1</sub>	30 mm

Shim 1.5°	279819 1
Overall length L	101.5 mm
Series	Eco
Functional width L <sub>4</sub>	25 mm
Shim screw	259027 6
Clamp, screw, O-ring	259036 15
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

---

## Accessories

Clamp unit Type 15	259036 15
Clamping screw	272500
Shim screw	272540
Shim screw Type 6	259027 6
Shim Type 1	279819 1