

Garant GRIDLINE

## ESD tool cabinet complete with drawers, 26×24G, Height mm / Model: 1000/10



### Order data

Order number	972440 1000/10
GTIN	4062406166885
Item class	9GK

### Description

#### Version:

Tool cabinet **ESD conductive**, to DIN EN 61340-5-1. Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Cabinet can be centrally locked by a cylinder lock. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time. **Includes ESD grounding cable.**

#### Fitted with:

Drawer front height, mm: 50, 75, 100, 100, 125, 250

#### Colour:

Body and drawers light grey similar to RAL 7035 **ESD powder-coated.**

#### Note:

- **When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.**
- **All plastic components (e.g. covering caps and handles) are non-ESD conductive.**

### Technical description

Drawer usable width	650 mm
---------------------	--------

Usable height	900 mm
ESD grounding cable included	yes
Height	1000 mm
Width	750 mm
Drawer usable depth in G	24
Drawer usable depth	600 mm
non-ESD conductive components	All plastic parts
Number of drawers	10
Depth	700 mm
ESD security	yes
Drawer usable width in G	26
Drawer usable area in G	26×24
Weight	196 kg
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	50 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular lock barrel
electrostatic characteristic	EGB/ESD
Product name attribute	26×24G
Type of product	Tool cabinet

## Accessories

Lock plate for GridLine Type HU21	914227 HU21
-----------------------------------	-------------