

Garant
eco clamping toolholder, right-hand, Shank size / insert size L: 20/16mm

Order data

Order number	271993 20/16
GTIN	4062406180768
Item class	21U

Description
Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability.

Supplied with:
With shim 1.5°.
Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No. 317900 – 319886.

Through-coolant: yes

Functional width L₄: 20 mm

Head length L₁: 30 mm

Overall length L: 89 mm

Shim 1.5°: 279819 1

Shim screw: 259027 6

Clamp, screw, O-ring: 259036 15

Technical description

Shank size	20 mm
Functional width L ₄	20 mm
Overall length L	89 mm

Head length L ₁	30 mm
Shim 1.5°	279819 1
suitable for insert size	16 mm
Series	Eco
Shim screw	259027 6
Clamp, screw, O-ring	259036 15
Application type	right-hand
Through-coolant	yes
Type of product	Boring bar

Accessories

Clamping screw	272500
Clamp unit Type 15	259036 15
Shim screw	272540
Shim screw Type 6	259027 6
Shim Type 1	279819 1