



Digital caliper ABS + accessories set, Measuring range:mm

Order data

Order number	412815
GTIN	4045197741318
Item class	42A

Description

Version:

Set consisting of a digital caliper and accessories set.

- **Digital caliper with absolute scale, no zeroing required. Large high-contrast digital display. The measuring faces are precision-lapped. With sturdy metal casing.**
- **Accessories set for digital caliper – permits measurement of recesses, slots and pitches between holes.**

Supplied with:

1× digital caliper No. 412821 size 150.

1 battery No. 081560 size CR2032.

1× accessory set No. 412747 size 3.5 **consisting of:**

2 pairs of contact point carriers short and long.

3 pairs of measuring tips with measuring discs Ø 6 mm, Ø 10 mm, Ø 12.5 mm.

2 pairs of measuring tips with anvil cones Ø 9 mm, 60° and Ø 12 mm, 60°.

1 pair of measuring tips with measuring cylinders Ø 1.5×9 mm.

1× spring system for constant gauging force.

1× hexagon key L-wrench.

1× depth extension base 75 mm.

Supplied in a sturdy plastic box.

Material: Stainless steel, INOX

all parts: hardened

Packaging: sturdy box

Norm: DIN 862

Reversible reading: mm / inch

Depth gauge: flat

Measured value saving: Once-off setting of the zero position

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 inch

Error limit: 0.03 mm

Jaw length: 40 mm

Technical description

Measurement method of the measuring instrument	
Packaging	sturdy box
IP Index of Protection	
Material	Stainless steel, INOX
Interface	
Measurement technology	digital
all parts	hardened
Type of product	Vernier caliper standard