


Indexable face mill 70° MFK, with bore, Ø D / number of teeth Z: 160/22mm

Order data

Order number	223300 160/22
GTIN	4960664732791
Item class	250

Description
Version:

Face mills for high-performance machining of cast iron. Close and very close tooth spacing for maximum productivity when machining cast iron.

Advantage:

- **Cost-effective and stable machining by use of 10-edge pentagonal inserts.**
- **Reduced cutting forces thanks to balanced tool design and high approach angle.**

Technical description

Wedge screw	229721
maximum external Ø D _{max}	169 mm
Overall length L _{tot}	63 mm
Cutting edge Ø D _c	160 mm
Mounting bore Ø	40 mm
suitable indexable insert	PN.. 1106
Wedge	229720

maximum cutting depth $a_{p\max}$	6 mm
Number of cutting edges Z	22
Shank type	with bore
Setting angle κ	70 degrees
Through-coolant	no
Type of product	Face mill

Accessories

Wedge screw	229721
Wedge	229720