

Garant
NC spotting drill HSS-E-PM 90° N, TiAlN, Ø DC h6: 5mm

Order data

Order number	112060 5
GTIN	4045197741509
Item class	11A

Description
Version:

≥ Ø 6 mm with **drive flat to DIN 1835-B**.

Precision centred ground point with thin chisel edge - gives easy spot drilling and high accuracy of the centre hole form. Very sturdy due to short flutes.

High-performance NC spotting drill.

Tool substrate made of sintered powder metallurgy **for applications** demanding high standards of tool life and accurate centring. Very good wear resistance in stainless steels.

Note:

Use speed for the actual hole Ø
(not necessarily the speed for the drill outer Ø).

Technical description

Feed f in steel < 900 N/mm ²	0.04 mm/rev.
Shank Ø D _s	5 mm
Nominal Ø D _c	5 mm
Shank tolerance	h6
Overall length L	60 mm
Flute length L _c	15 mm
Shank	DIN 1835 B to h6
Coating	TiAlN
Tool material	HSS E PM
Standard	Manufacturer's standard

Type	N
Tolerance nominal \varnothing	h6
Point angle	90 degrees
Number of cutting edges Z	2
Through-coolant	no
Colour ring	without
Type of product	Spotting drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	96 m/min	N
Aluminium (short chipping)	suitable	62 m/min	N
Alu > 10% Si	suitable	55 m/min	N
Steel < 500 N/mm ²	suitable	55 m/min	P
Steel < 750 N/mm ²	suitable	42 m/min	P
Steel < 900 N/mm ²	suitable	35 m/min	P
Steel < 1100 N/mm ²	suitable	14 m/min	P
Steel < 1400 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	18 m/min	M
INOX > 900 N/mm ²	suitable	13 m/min	M
Ti > 850 N/mm ²	suitable	8 m/min	S
GG(G)	suitable	35 m/min	K
CuZn	suitable	112 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		