


**Indexable face mill 70° MFK, with bore, Ø D / number of teeth Z: 125/12mm**

**Order data**

Order number	223300 125/12
GTIN	4960664732760
Item class	250

**Description**
**Version:**

Face mills for high-performance machining of cast iron. Close and very close tooth spacing for maximum productivity when machining cast iron.

**Advantage:**

- **Cost-effective and stable machining by use of 10-edge pentagonal inserts.**
- **Reduced cutting forces thanks to balanced tool design and high approach angle.**

**Technical description**

Number of cutting edges Z	12
Cutting edge Ø D <sub>c</sub>	125 mm
suitable indexable insert	PN.. 1106
Overall length L <sub>tot</sub>	63 mm
Wedge	229720
Wedge screw	229721
maximum cutting depth a <sub>p max</sub>	6 mm

maximum external $\varnothing D_{\max}$	134 mm
Mounting bore $\varnothing$	40 mm
Shank type	with bore
Setting angle $\kappa$	70 degrees
Through-coolant	no
Type of product	Face mill

---

## Accessories

Wedge screw	229721
Wedge	229720