

Garant

Jobber drill extra long HSS N, uncoated, Ø DC h8 × overall length L: 4X175mm



Order data

Order number	116245 4X175
GTIN	4045197745743
Item class	11B

Description

Version:

With precision ground point.

Vaporised high performance drills for drilling particularly deep holes. Take particular care to ensure **frequent chip clearance**.

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

Suitable NC spotting drills No. 112103, 112110 and 112160 with **120° tip angle** for enhanced process reliability

Technical description

Flute length L_c	120 mm
Standard	DIN 1869
Feed f in steel $< 750 \text{ N/mm}^2$	0.05 mm/rev.
Shank $\varnothing D_s$	4 mm
Number of cutting edges Z	2
Nominal $\varnothing D_c$	4 mm
Tolerance nominal \varnothing	h8
Overall length L	175 mm
recommended maximum drilling depth L_2	114 mm
Point angle	118 degrees

Shank	Plain shank
Coating	uncoated
Tool material	HSS
Type	N
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	50 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	32 m/min	N
Steel < 500 N/mm ²	suitable	28 m/min	P
Steel < 750 N/mm ²	suitable	21 m/min	P
Steel < 900 N/mm ²	suitable	18 m/min	P
Steel < 1100 N/mm ²	suitable	5 m/min	P
GG(G)	suitable	18 m/min	K
Oil	suitable		
wet maximum	suitable		