

**Garant****Solid carbide torus cutter R1 0.1, Diamond, Ø DC × L1: 2X16mm****Order data**

Order number	209716 2X16
GTIN	4062406187941
Item class	11Y

**Description****Version:**

With **crystalline diamond sp<sup>3</sup> coating**. For the **highest demands regarding performance and precision** in fibre-reinforced composites, CRP, GRP, and graphite. **Extremely tight tolerances** ensure maximum accuracy. Double relief ground with 2 hollow-ground chamfers. **Recess angle  $\alpha = 16^\circ$** .

Tolerances:

- **Corner radius:  $R_1 = \pm 0.0025$  mm**
- **Neck Ø:  $D_1 = 0 / -0.01$  mm**

**Note:**

At greater tool overhang lengths, use a reduced value for  $a_p$ !

Values for:

copying:  $a_p = 0.10 \times D \times a_{p, \text{korr}}$ side milling:  $a_p = 0.20 \times D \times a_{p, \text{korr}}$ 

**To calculate the feed rate  $vf$  please use the actual speed of the machine (the maximum possible speed)!**

e.g:  $vf = 18000$  [rpm] ×  $fz$  [mm/Z] ×  $z$

**Technical description**

Flute length $L_c$	2 mm
Corner radius $R_1$	0.1 mm
No. of teeth $Z$	2
Overhang length $L_1$ incl. recess	16 mm
Shank Ø $D_s$	4 mm
Cutting edge Ø $D_c$	2 mm

## Data sheet

Helix angle	30 degrees
Overall length L	55 mm
Shank	DIN 6535 HA to h5
Coating	Diamond
Tool material	Solid carbide
Standard	Manufacturer's standard
Tolerance nominal $\varnothing$	0 / -0.005
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	0.05×D for copy milling
Cutting width $a_e$ for milling operation	0.5×D for side milling
Through-coolant	no
Colour ring	black
Type of product	Torus cutter

### User data

	Suitability	$V_c$	ISO code
PVDF GF20	suitable	200 m/min	N
POM GF25	suitable	190 m/min	N
PA 66 GF30	suitable	170 m/min	N
PEEK GF30	suitable	150 m/min	N
PTFE CF25	suitable	180 m/min	N
PEEK CF30	suitable	160 m/min	N
Hybrids	suitable		
Honeycomb sandwich	suitable	350 m/min	N
GRP	suitable	190 m/min	N
GRP, CRP	suitable	190 m/min	N
Graphite	suitable	340 m/min	N
wet minimum	suitable		
dry	suitable		

Air

suitable