

Garant
Solid carbide reamer HPC through hole, TiAlN, Nominal Ø DC: 4H7mm

Order data

Order number	164350 4H7
GTIN	4045197743732
Item class	10N

Description
Version:

Version suitable for NC with straight shank Ø for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

Reamers finish ground to match your specifications.

With short flutes and left-hand helix.

Application:

For **HPC/HSM reaming** of **through holes**.

Note:
NEW GENERATION AVAILABLE!
Recommended successor product is No. 164420.

Application for type of drilling: for through holes

Bore Ø tolerance: H7

Number of cutting edges Z: 4

Bore Ø tolerance: H7

Flute length L_c: 12 mm

Overhang L₁: 34 mm

Overall length L: 75 mm

Number of cutting edges Z: 4

Shank Ø D_s: 6 mm

Technical description

Overhang L ₁	34 mm
Overall length L	75 mm

Feed f in stainless steel < 900 N/mm ²	0.06 mm/rev.
Shank Ø D _s	6 mm
Nominal Ø D _c	4 mm
Flute length L _c	12 mm
Number of cutting edges Z	4
Shank tolerance	h6
recommended drill Ø in INOX < 900 N/mm ²	3.9 mm
Bore Ø tolerance	H7
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for through holes
Colour ring	blue
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
INOX < 900 N/mm ²	suitable	30 m/min	M
INOX > 900 N/mm ²	suitable	25 m/min	M
Oil	suitable		
wet maximum	suitable		