

**Garant**
**Solid carbide milling cutter, TiAlN, Ø e8 DC: 4mm**

**Order data**

Order number	202725 4
GTIN	4045197746429
Item class	11X

**Description**
**Version:**

Double relief ground side clearance angle.

**Without** 45° cutting edge chamfer.

**Technical description**

Recess Ø D <sub>1</sub>	3.8 mm
Shank form	HA
Cutting edge Ø D <sub>c</sub>	4 mm
Direction of infeed	horizontal, oblique and vertical
Flute length L <sub>c</sub>	12 mm
Overhang length L <sub>1</sub> incl. recess	18 mm
No. of teeth Z	4
Feed f <sub>z</sub> for slot milling in steel < 900 N/mm <sup>2</sup>	0.02 mm
Shank Ø D <sub>s</sub>	4 mm
Feed f <sub>z</sub> for side milling in steel < 900 N/mm <sup>2</sup>	0.023 mm
Shank	DIN 6535 HA to h6
Overall length L	40 mm
Helix angle	30 degrees
Corner chamfer angle	90 degrees

Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	280 m/min	N
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 55 HRC	suitable	35 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	Suitable		
wet minimum	Suitable only under restricted conditions		
dry	suitable		
Air	Suitable		

