

## Garant

**GARANT Softcut® 90° shoulder mill MTC, with threaded shank, Ø D / number of teeth Z: 40/4mm**



### Order data

Order number	215570 40/4
GTIN	4045197750723
Item class	210

### Description

#### Version:

High precision indexable face mill with irregular pitch for very smooth cutting, very high precision, and very high metal removal rate. **New generation** of high performance indexable face mills **with special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or **for spindles with low drive power**.

#### Application:

For face milling to large depths, also slotting. General use in all steels including stainless steels.

#### Spare part:

Pack of insert screws No. 219826 (8IP; 2.2 Nm).

#### Note:

The insert pocket must be modified when using indexable inserts with a radius greater than 2 mm.

GARANT torque screwdriver TQ No. **211750 size 2.2**, use bit No. **674252 size 8IP**.

### Technical description

Cutting edge Ø D <sub>c</sub>	40 mm
Ø D <sub>2</sub>	28.7 mm
Ø D <sub>1</sub> h6	17 mm
Pack of insert screws	219826 (8IP; 2.2 Nm)

Overall length $L_{tot}$	40 mm
Mounting thread M	M16
Number of cutting edges Z	4
suitable indexable insert	AP.. 1335..
Circular interpolation milling $\varnothing D_{max}$	78 mm
Circular interpolation milling $a_p$	1.8 mm
Circular interpolation milling $\varnothing D_{min}$	77 mm
Ramping angle $\alpha_{max}$	0.5 degrees
Ramping length L for $\alpha_{max}$	34.5 mm
Series	Softcut®
$\varnothing D_3$	37 mm
Shank type	with threaded shank
Setting angle $\kappa$	90 degrees
Milling application	Circular milling
Milling application	Circular milling
Milling application	Ramping
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2