



Copy milling cutter 7° positive, with bore, Ø D / number of teeth Z: 66/6_ mm

Order data

Order number	212150 66/6_
GTIN	4045197750402
Item class	210

Description

Version:

Milling body with irregular pitch for smooth cutting.

- **High axial run-out accuracy and concentricity**
- **Stepless repositioning as the cutting edge wears.**

Vibration reduction and soft cutter edge entry due to 7° positive setting of the indexable inserts.

Attention:

Retaining screws and retaining washers should **not** be used for inserts with positive geometry.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**.

$a_{p\ max} = 4.0\ mm$.

Milling head suitable for insert shape: round

Milling application: Ramping

Milling application: Circular milling

Spacing of the milling cutter's cutting edges: unequal spacing

Tool exchange: PowerCard

Technical description

Tool exchange	PowerCard
Machining strategy	
Milling head suitable for insert shape	round
Shank type	with bore
Milling application	Ramping
Milling application	Circular milling
Spacing of the cutters	unequal spacing
Setting angle κ	

Type of product
