

Garant**FeedKing high feed rate milling cutter with bore, for indexable inserts XD..****Order data**

Order number	212910 35/5
GTIN	4045197750624
Item class	210

Description**Version:**

Dynamic cutting edge geometry for highest feed rates. Extremely smooth cutting due to **self-stabilising insert bedding**. **Optimised geometry** for reduced cutting forces, thereby reducing the stress on the main spindle.

Advantage:

Particularly cost-effective due to **exceptionally sturdy 4-edge** inserts.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 9IP**.

Technical description

suitable indexable insert	XD.. 070308
Cutting edge $\varnothing D_c$	35 mm
Set of insert screws	219810 (9IP; 2.2 Nm)
Number of cutting edges Z	5
maximum cutting depth $a_{p\max}$	0.85 mm
Mounting bore \varnothing	16 mm
$\varnothing D_3$	22 mm

Overall length L_{tot}	40 mm
Through-coolant	yes
Circular interpolation milling $\varnothing D_{\text{min}}$	57 mm
Circular interpolation milling $\varnothing D_{\text{max}}$	68 mm
Circular interpolation milling a_p	0.85 mm
Ramping length L for α_{max}	21 mm
Ramping angle α_{max}	0.82 degrees
Series	FeedKing
Setting angle κ	10 degrees
Fz Helix	0.7
Shank type	with bore
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Spacing of the cutters	unequal spacing
Machining strategy	HPC
Tool exchange	PowerCard
Type of product	Copy mill

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/212910-35/5>