

Garant

**GARANT Softcut® 90° shoulder mill MTC, with bore, Ø D / number of teeth Z:
42/5mm**



Order data

Order number	215575 42/5
GTIN	4045197750754
Item class	210

Description

Version:

High precision indexable face mill with irregular pitch for very smooth cutting, very high precision, and very high metal removal rate. **New generation** of high performance indexable face mills **with special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or **for spindles with low drive power**.

Application:

For face milling to large depths, also slotting. General use in all steels including stainless steels.

Spare part:

Pack of insert screws No. 219826 (8IP; 2.2 Nm).

Note:

The insert pocket must be modified when using indexable inserts with a radius greater than 2 mm.

GARANT torque screwdriver TQ No. **211750 size 2.2**, use bit No. **674252 size 8IP**.

Technical description

suitable indexable insert	AP.. 1335..
Overall length L_{tot}	40 mm

Pack of insert screws	219826 (8IP; 2.2 Nm)
Cutting edge $\varnothing D_c$	42 mm
Number of cutting edges Z	5
Mounting bore \varnothing	16 mm
Ramping angle α_{max}	0.47 degrees
Circular interpolation milling a_p	1.8 mm
Ramping length L for α_{max}	36.5 mm
Circular interpolation milling $\varnothing D_{min}$	81 mm
Circular interpolation milling $\varnothing D_{max}$	82 mm
Series	Softcut®
$\varnothing D_3$	39 mm
Shank type	with bore
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Circular milling
Milling application	Ramping
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP