

**Garant**
**Solid carbide HPC drill Weldon shank DIN 6535 HB, DLC, Ø DC h7: 9,6mm**


## Order data

|              |               |
|--------------|---------------|
| Order number | 122603 9,6    |
| GTIN         | 4045197758170 |
| Item class   | 11E           |

## Description

### Version:

**DLC coating sp<sup>2</sup>** of the latest generation with **low coefficient of friction** results in **outstanding chip clearance**. For **high-performance milling** of **aluminium materials**. **High roundness** and **alignment accuracy of the deep hole**, thanks to **6 guide chamfers**.

### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

## Technical description

|  |               |
|--|---------------|
| Number of cutting edges Z                | 2             |
| Shank tolerance                          | h6            |
| Standard                                 | DIN 6537      |
| Flute length $L_c$                       | 61 mm         |
| Feed f in aluminium short-chipping       | 0.55 mm/rev.  |
| Overall length L                         | 103 mm        |
| Tolerance nominal Ø                      | h7            |
| Shank Ø $D_s$                            | 10 mm         |
| Nominal Ø $D_c$                          | 9.6 mm        |
| recommended maximum drilling depth $L_2$ | 46.6 mm       |
| Coating                                  | DLC           |
| Tool material                            | solid carbide |

|                    |                   |
|--------------------|-------------------|
| Version            | 6xD               |
| Type               | W                 |
| Point angle        | 135 degrees       |
| Shank              | DIN 6535 HB to h6 |
| Through-coolant    | Yes, with 25 bar  |
| Machining strategy | HPC               |
| Semi-Standard      | yes               |
| Colour ring        | yellow            |
| Type of product    | Jobber drill      |

### User data

|                            | Suitability | V <sub>c</sub> | ISO code |
|----------------------------|-------------|----------------|----------|
| Alu plastics               | suitable    | 360 m/min      | N        |
| Aluminium (short chipping) | suitable    | 400 m/min      | N        |
| Alu > 10% Si               | suitable    | 350 m/min      | N        |
| PMMA acrylic               | suitable    | 150 m/min      | N        |
| PEEK                       | suitable    | 120 m/min      | N        |
| PVDF GF20                  | suitable    | 90 m/min       | N        |
| PA 66 GF30                 | suitable    | 80 m/min       | N        |
| PEEK GF30                  | suitable    | 70 m/min       | N        |
| PTFE CF25                  | suitable    | 80 m/min       | N        |
| Cu                         | suitable    | 160 m/min      | N        |
| CuZn                       | suitable    | 200 m/min      | N        |
| GRP                        | suitable    | 80 m/min       | N        |
| CRP                        | suitable    | 80 m/min       | N        |
| wet maximum                | suitable    |                |          |
| wet minimum                | suitable    |                |          |

