

Garant
Solid carbide HPC drill, plain shank DIN 6535 HA, DLC, Ø DC h7: 2,2mm

Order data

| | |
|--------------|---------------|
| Order number | 123178 2,2 |
| GTIN | 4045197754783 |
| Item class | 11E |

Description
Version:

DLC coating sp² of the latest generation with **low coefficient of friction** results in **outstanding chip clearance**. For **high-performance milling** of **aluminium materials**. **High roundness** and **alignment accuracy of the deep hole**, thanks to **6 guide chamfers**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

For process reliability when using the 12xD drill, an initial centre drilling with NC spotting drills No. 121068– 121130 is necessary.

Form HB and HE are supplied at the same price as HA.

Order form **HB**: with **No. 123179**.

Order form **HE**: with **No. 123178 + 129100HE**.

Technical description

| | |
|------------------------------------|-------------------------|
| Overall length L | 72 mm |
| Feed f in aluminium short-chipping | 0.22 mm/rev. |
| Number of cutting edges Z | 2 |
| Tolerance nominal Ø | h7 |
| Shank tolerance | h6 |
| Nominal Ø D _c | 2.2 mm |
| Standard | Manufacturer's standard |
| Flute length L _c | 34 mm |
| Shank Ø D _s | 4 mm |

| | |
|---|-------------------|
| recommended maximum drilling depth L ₂ | 30.7 mm |
| Coating | DLC |
| Tool material | solid carbide |
| Version | 12×D |
| Type | W |
| Point angle | 135 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | yellow |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|----------------------------|-------------|----------------|----------|
| Alu plastics | suitable | 250 m/min | N |
| Aluminium (short chipping) | suitable | 280 m/min | N |
| Alu > 10% Si | suitable | 245 m/min | N |
| PMMA acrylic | suitable | 105 m/min | N |
| PEEK | suitable | 85 m/min | N |
| PVDF GF20 | suitable | 60 m/min | N |
| PA 66 GF30 | suitable | 55 m/min | N |
| PEEK GF30 | suitable | 50 m/min | N |
| PTFE CF25 | suitable | 55 m/min | N |
| Cu | suitable | 120 m/min | N |
| CuZn | suitable | 150 m/min | N |
| GRP | suitable | 55 m/min | N |
| CRP | suitable | 55 m/min | N |

| | |
|-------------|----------|
| wet maximum | suitable |
| wet minimum | suitable |