

Garant
Solid carbide HPC drill Weldon shank DIN 6535 HB, DLC, Ø DC h7: 16,5mm


Order data

Order number	122603 16,5
GTIN	4045197758446
Item class	11E

Description

Version:

DLC coating sp² of the latest generation with **low coefficient of friction** results in **outstanding chip clearance**. For **high-performance milling** of **aluminium materials**. **High roundness** and **alignment accuracy of the deep hole**, thanks to **6 guide chamfers**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$

Technical description

Shank tolerance	h6
Flute length L_c	93 mm
Standard	DIN 6537
Nominal Ø D_c	16.5 mm
Overall length L	143 mm
Feed f in aluminium short-chipping	0.7 mm/rev.
Number of cutting edges Z	2
Tolerance nominal Ø	h7
Shank Ø D_s	18 mm
recommended maximum drilling depth L_2	68.3 mm
Coating	DLC
Tool material	solid carbide

Version	6xD
Type	W
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	Yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	360 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	350 m/min	N
PMMA acrylic	suitable	150 m/min	N
PEEK	suitable	120 m/min	N
PVDF GF20	suitable	90 m/min	N
PA 66 GF30	suitable	80 m/min	N
PEEK GF30	suitable	70 m/min	N
PTFE CF25	suitable	80 m/min	N
Cu	suitable	160 m/min	N
CuZn	suitable	200 m/min	N
GRP	suitable	80 m/min	N
CRP	suitable	80 m/min	N
wet maximum	suitable		
wet minimum	suitable		

