



Solid carbide HPC drill plain shank DIN 6535 HA, DLC, Ø p6: 4,7 mm

Order data

Order number	122606 4,7
GTIN	4045197756008
Item class	11E

Technical description

Type	W
Tool material	Solid carbide
Helix angle	degrees
Through-coolant	yes, with 25 bar
Drill depth up to	6×D
Use for drilling	
Cutting direction	
Machining strategy	HPC
Coating	DLC
Hole tolerance	
Point angle	140 degrees
Colour ring	yellow
Pilot drill required	
Schaft	DIN 6535 HA to h6
Series	
Type of product	

