

## Garant

**Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC m6 (Ø DC X = h7)  
(mm or inch): 2,1**



### Order data

Order number	122659 2,1
GTIN	4045197582379
Item class	11E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. High roundness and alignment accuracy of the deep hole, thanks to **4 guide chamfers**. Outstanding chip evacuation due to **4 internal cooling channels** from Ø 3.8 mm. Up to 3.7 mm Ø with 2 internal cooling channels. **Straight major cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

#### Attention:

Sizes **ending with X** = cutter Ø tolerance **h7**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122661**.

Form **HE**: order with **No. 122659 + 129100HE**.

Standard: DIN 6537

Tolerance nominal Ø: m6

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 17.9 mm

Tolerance nominal Ø: m6

Overall length L: 57 mm

Shank Ø  $D_s$ : 4 mm

Feed f in stainless steel > 900 N/mm<sup>2</sup>: 0.05 mm/rev.

### Technical description

Shank tolerance	h6
Nominal Ø $D_c$	2.1 mm

Feed f in stainless steel > 900 N/mm <sup>2</sup>	0.05 mm/rev.
Flute length L <sub>c</sub>	21 mm
Number of cutting edges Z	2
Tolerance nominal Ø	m6
Shank Ø D <sub>s</sub>	4 mm
Overall length L	57 mm
Standard	DIN 6537
recommended maximum drilling depth L <sub>2</sub>	17.9 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	140°
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	blue
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	130 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	70 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	80 m/min	M
GG(G)	suitable	95 m/min	K

wet maximum	suitable
wet minimum	suitable
Air	suitable