

**Garant**
**Solid carbide HPC drill, plain shank DIN 6535 HA, DLC, Ø DC h7: 4,3mm**

**Order data**

Order number	122602 4,3
GTIN	4045197752482
Item class	11E

**Description**
**Version:**

**DLC coating sp<sup>2</sup>** of the latest generation with **low coefficient of friction** results in **outstanding chip clearance**. For **high-performance milling** of **aluminium materials**. **High alignment accuracy** and **roundness of the hole**, thanks to **6 guide chamfers**.

Size 1 - 1.5 with 4 guide chamfers.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122603**.

Form **HE**: order with **No. 122602 + 129100HE**.

**Technical description**

Nominal Ø D <sub>c</sub>	4.3 mm
Flute length L <sub>c</sub>	36 mm
Shank tolerance	h6
Overall length L	74 mm
Tolerance nominal Ø	h7
Number of cutting edges Z	2
Feed f in aluminium short-chipping	0.35 mm/rev.
Shank Ø D <sub>s</sub>	6 mm
Standard	DIN 6537
recommended maximum drilling depth L <sub>2</sub>	29.6 mm

Coating	DLC
Tool material	solid carbide
Version	6xD
Type	W
Point angle	135 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	360 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	350 m/min	N
PMMA acrylic	suitable	150 m/min	N
PEEK	suitable	120 m/min	N
PVDF GF20	suitable	90 m/min	N
PA 66 GF30	suitable	80 m/min	N
PEEK GF30	suitable	70 m/min	N
PTFE CF25	suitable	80 m/min	N
Cu	suitable	160 m/min	N
CuZn	suitable	200 m/min	N
GRP	suitable	80 m/min	N
CRP	suitable	80 m/min	N
wet maximum	suitable		

wet minimum  
**Services**

suitable

Shank grinding Type HE

129100 HE