

Garant
Shrink-fit chuck with cooling channel bores and strengthened walls, SK 40 short, Clamping range Ø D1: 12 mm

Order data

Order number	302316 12
GTIN	4045197762443
Item class	31A

Description
Version:

- Supplied with coolant supply holes that can be plugged.
- High-temperature steel.
- Integral tool length adjustment, adjustment track 10 mm.
- For HSS and carbide.
- Shanks hard turned (for smooth running!)
- With Balluffchip bore.
- Glass bead blasted.

Advantage:

The reinforced version

- permits better machining results (feed rate, depth of cut).
- achieves better workpiece surface quality (due to vibration damping effect).

Application:

For clamping tools with parallel shank to h6 tolerance. Suitable for inductive, contact and hot-air shrink units.

Optional extras:

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450.

Cooling channel bore: lockable

Overhang dimension A: 65 mm

Ø D₂: 26.5 mm

Ø D₃: 32.9 mm

L₁: 47 mm

Technical description

L ₁	47 mm
Ø D ₃	32.9 mm
Ø D ₂	26.5 mm
Clamping Ø D ₁	12 mm
Overhang dimension A	65 mm
Cooling channel bore	lockable
Adapter	SK 40 short
Arbor standard	DIN 69871
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Machining strategy	HSC
Type of product	Shrink-fit chuck

Accessories

Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 25/12 mm	302410 25/12
Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK	308812 40
Shrink-fit chuck extension 4.5° without length adjustment screw Ø d / Ø D1 32/12 mm	302416 32/12
Pull stud, 18CrNiMo7 sealed, form B suitable for steep tapers 40	308615 40
Cooling adapter short 4.5° for clamping Ø 9,1-12 mm	354235 9,1-12
Basic tool mounting for SK for taper shank 40 SK	354225 40

Pull stud Form A suitable for steep tapers 40	308600 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Pull stud sealed, form B suitable for steep tapers 40	308620 40
Shrink fit chuck extension 3°, vibration-damped $\varnothing d / \varnothing D1$ 20/12 mm	302415 20/12
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud sealed, form B suitable for steep tapers 40	308650 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Shrink-fit chuck extension 4.5° with length adjustment screw $\varnothing d / \varnothing D1$ 25/12 mm	302412 25/12
Shrink-fit chuck extension 4.5° without length adjustment screw, with through coolant holes $\varnothing d / \varnothing D1$ 32/12 mm	302414 32/12
Screening plate for coil SU1 for clamping \varnothing 12-20 mm	354240 12-20
Shrink-fit chuck extension 4.5° without length adjustment screw $\varnothing d / \varnothing D1$ 25/12 mm	302416 25/12
Shrink-fit chuck extension 4.5° without length adjustment screw $\varnothing d / \varnothing D1$ 32/12 mm	302410 32/12
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308700 40
Cooling adapter long 4.5° for clamping \varnothing 9,1-12 mm	354236 9,1-12
Pull stud sealed suitable for steep tapers 40	308660 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308810 40
Pull stud stud sealed, form A suitable for steep tapers 40	308610 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull stud Mori-Seiki, sealed, form A suitable for steep tapers 40	308625 40

Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Shrink-fit unit Type SU1	354210 SU1
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud, 18CrNiMo7 Form A suitable for steep tapers 40	308605 40
Screening plate for coil SU1 for clamping Ø 6-12 mm	354240 6-12
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for steep tapers 40 SK	308820 40
Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 25/12 mm	302417 25/12
Shrink-fit chuck extension 4.5° with length adjustment screw Ø d / Ø D1 32/12 mm	302412 32/12
Pull stud Mazak sealed, form A suitable for steep tapers 40M	308670 40M
Pull stud Form B suitable for steep tapers 40	308640 40
Wrench for pull studs ISO 7388 suitable for steep tapers 40 SK	308830 40
Cooling unit Type CU1	354215 CU1
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Special pull stud with no internal thread sealed suitable for steep tapers 40	308720 40
Pull stud sealed suitable for steep tapers 40	308635 40