

Garant

Face mill arbor Form ADB with cooling channel bore, SK 40 A = 120, Spigot Ø d1: 40mm


Order data

Order number	301035 40
GTIN	4045197762894
Item class	31A

Description
Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- Short series.
- Increased collar contact surface.
- With RFID/Balluffchip bore.
- With 4 cooling channel bores.
- All shanks hard turned (for smooth running!).

Supplied with:

Lock screw

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Technical description

Spigot Ø d ₁	40 mm
Overhang dimension A	120 mm
External Ø D	89 mm
Milling mandrel length L ₄	27 mm
Suitable toggle spanner No. 309840	40

Spare milling cutter lock screw No. 309860 / 309861	40
Clamping $\varnothing D_1$	40 mm
Adapter	SK 40 A = 120
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	ADB
Cooling channel bore	cannot be plugged
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Pull studsealed, form B suitable for steep tapers 40	308620 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
	308801 40

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

Special pull stud with no internal threadsealed suitable for steep tapers 40

308700 40

Milling cutter lock screw for mandrel Ø 40 mm

309860 40

Pull studForm B suitable for steep tapers 40

308640 40

Special pull stud with internal thread suitable for steep tapers 40

308740 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

308625 40

Toggle spanner for mandrel Ø 40 mm

309840 40

Pull stud 45°sealed suitable for steep tapers 40

308760 40

Pull stud 90°sealed suitable for steep tapers 40

308790 40

Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40

308820 40

Pull stud 60°sealed suitable for steep tapers 40

308785 40

Pull studsealed suitable for steep tapers 40

308635 40

Pull studsealed suitable for steep tapers 40

308660 40

Pull studMazak, form A suitable for steep tapers 40M

308670 40M

Pull studForm A suitable for steep tapers 40

308600 40