

Garant
Face mill arbor with cooling channel bore, HSK-A 63 medium, Spigot \varnothing d1: 16mm

Order data

Order number	306541 16
GTIN	4045197763532
Item class	31A

Description
Version:

- Clamping \varnothing 40 with 4 tapped holes for drive blocks to DIN 2079.
- With RFID/Balluffchip bore.
- Increased collar contact surface.
- HSK mating faces machined.

With **cooling channel bore**.

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Coolant tube No. 309880, socket wrench No. 309890, toggle spanner No. 309840, milling cutter lock screw for internal coolant supply No. 309861.

Technical description

Overhang dimension A	75 mm
Spigot \varnothing d ₁	16 mm
External \varnothing D	38 mm
Spare milling cutter lock screw No. 309860 / 309861	16

Milling mandrel length L ₄	17 mm
Suitable toggle spanner No. 309840	16
Clamping Ø D ₁	16 mm
Adapter	HSK-A 63 medium
Arbor standard	DIN 69893
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Shape	A
Cooling channel bore	cannot be plugged
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 16 mm	309840 16
Milling cutter lock screw for mandrel Ø 16 mm	309860 16