

Garant
Face mill arbor cylindrical, SK 40 A = 200, Spigot Ø d1: 22mm


Order data

Order number	301136 22
GTIN	4045197761293
Item class	31A

Description

Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- With RFID / Balluffchip bore.
- Larger collar contact face.

Vibration damped version, arbor with vibration-damping core.

Advantage:

Significantly lower tendency to vibrate! Considerable increase in feed rate!

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Note:

Further sizes on request.

Technical description

Milling mandrel length L ₄	19 mm
Overhang dimension A	200 mm
Ø D ₂	48 mm
Weight	3 kg
Adapter	SK 40 A = 200
Standard	DIN 6357

Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

Accessories

Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Pull studForm B suitable for steep tapers 40	308640 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studsealed suitable for steep tapers 40	308660 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Toggle spanner for mandrel Ø 40 mm	309840 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Toggle spanner for mandrel Ø 22 mm	309840 22
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull studsealed, form B suitable for steep tapers 40	308620 40

Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studsealed suitable for steep tapers 40	308635 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40