

Garant
Face mill arbor vibration-damped, cylindrical, HSK-A 63 A = 300, Spigot Ø d1: 16mm

Order data

Order number	306706 16
GTIN	4045197761958
Item class	31A

Description
Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- With Balluff/RFID chip bore.
- Increased collar contact surface.

Vibration damped version, arbor with vibration-damping core.

Advantage:

Significantly lower tendency to vibrate! Considerable increase in feed rate!

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Special coolant pipe wrench No. 309840, coolant pipe No. 309880.

Note:

Further sizes on request.

Technical description

Ø D ₂	38 mm
Overhang dimension A	300 mm
Milling mandrel length L ₄	17 mm
Adapter	HSK-A 63 A = 300
Standard	DIN 6357
Arbor standard	DIN 69893

Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 16 mm	309840 16
------------------------------------	-----------