



## Short drill chuck Form A, SK 30, Clamping range: 0,5-13mm



### Order data

Order number	301478 0,5-13
GTIN	2050001838902
Item class	33W

### Description

#### Version:

For clockwise and anticlockwise rotation.

#### Supplied with:

Hexagon screwdriver with T-handle.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

Spare chuck key No. 627425	6AF
Clamping range	0.5 - 13 mm
External Ø D	50 mm
Overhang dimension A	111 mm
Adapter	SK 30
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 18,000 rpm
Concentricity	≤ 30 µm
Type of product	Short drill chuck

