

Garant
Solid carbide HPC drill, plain shank DIN 6535 HA, DLC, Ø DC h7: 8,8mm

Order data

Order number	123178 8,8
GTIN	4045197755445
Item class	11E

Description
Version:

DLC coating sp^2 of the latest generation with **low coefficient of friction** results in **outstanding chip clearance**. For **high-performance milling** of **aluminium materials**. **High roundness** and **alignment accuracy of the deep hole**, thanks to **6 guide chamfers**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

For process reliability when using the 12xD drill, an initial centre drilling with NC spotting drills No. 121068– 121130 is necessary.

Form HB and HE are supplied at the same price as HA.

Order form **HB**: with **No. 123179**.

Order form **HE**: with **No. 123178 + 129100HE**.

Technical description

Nominal Ø D_c	8.8 mm
Shank tolerance	h6
Flute length L_c	120 mm
Standard	Manufacturer's standard
Shank Ø D_s	10 mm
Number of cutting edges Z	2
Feed f in aluminium short-chipping	0.55 mm/rev.
Tolerance nominal Ø	h7
Overall length L	162 mm

recommended maximum drilling depth L ₂	106.8 mm
Coating	DLC
Tool material	solid carbide
Version	12×D
Type	W
Point angle	135 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	250 m/min	N
Aluminium (short chipping)	suitable	280 m/min	N
Alu > 10% Si	suitable	245 m/min	N
PMMA acrylic	suitable	105 m/min	N
PEEK	suitable	85 m/min	N
PVDF GF20	suitable	60 m/min	N
PA 66 GF30	suitable	55 m/min	N
PEEK GF30	suitable	50 m/min	N
PTFE CF25	suitable	55 m/min	N
Cu	suitable	120 m/min	N
CuZn	suitable	150 m/min	N
GRP	suitable	55 m/min	N
CRP	suitable	55 m/min	N

wet maximum	suitable
wet minimum	suitable

Services

Shank grinding Type HE	129100 HE
------------------------	-----------