

**Garant****SNMG 150616, Grade: HB7020**

## Order data

Order number	251332 HB7020
GTIN	4045197764195
Item class	21G

## Description

SNMG 150616 HB7020 Corner radius: 1.6 mm  
Grade: HB7020  
Chip breaker: SG  
Cutting depth  $a_p$ : 1.5 - 9 mm  
Feed  $f$ : 0.25 - 0.8 mm/rev.  
Cutting speed  $v_c$  main application: 100 - 300 m/min

## Technical description

Corner radius	1.6 mm
Feed $f$	0.25 - 0.8 mm/rev.
Cutting depth $a_p$	1.5 - 9 mm
Cutting conditions	slightly interrupted
Main application	P
Chip breaker	SG
Grade	HB7020

Cutting speed $v_c$ main application	100 - 300 m/min
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMG 150616
Number of changes/inserts	8
Type of product	Indexable insert for turning