


Garant
WNMG 080412, Grade: HB7020


Order data

Order number	252072 HB7020
GTIN	4045197764249
Item class	21G

Description

WNMG 080412 HB7020 Grade: HB7020

Chip breaker: SM

Tolerance: M

Cutting depth a_p : 0.5 - 4 mm

Feed f : 0.2 - 0.5 mm/rev.

Cutting speed v_c main application: 120 - 350 m/min

Technical description

Corner radius	1.2 mm
Feed f	0.2 - 0.5 mm/rev.
Grade	HB7020
Cutting depth a_p	0.5 - 4 mm
Cutting conditions	slightly interrupted
Chip breaker	SM
Main application	P

Cutting speed v_c main application	120 - 350 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	WNMG 080412
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning