

**Garant****Torque screwdriver, fixed setting, set torque: 1,0N·m**

## Order data

Order number	211750 1,0
GTIN	4045197764263
Item class	21B

## Description

**Version:**

Torque screwdriver with easy-grip 2-component T-handle. The torque is fixed. Toolholder with permanent magnet.

**Function:**

When the torque is reached the screwdriver triggers **with clearly audible and perceptible signal**. The long-travel indication gives the user an unmistakable signal that the set torque has been reached.

**Application:**

In conjunction with **1/4 inch bits** with **C 6.3** or **E 6.3 shank**, e.g. **Torx Plus® bit No. 674252**. Ideal for precise tightening of indexable inserts to the specified torque.

**Standard:**

Geprüft nach DIN EN ISO 6789.

**Note:**

Supplied **without** bit.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

## Technical description

set torque	1 Nm
Torque measuring accuracy	±15 %
Blade length	50 mm
Bit socket	D 6,3
Bit socket	F 6.3
Overall length L	107 mm
Measurement process	Torque
Adjustable trigger value	non-adjustable
Setting the trigger value	preset
Reversible reading	Nm
Standard	DIN EN ISO 6789
Feedback	triggering
Connection format	Bit holder 1/4 inch
Trigger principle	Mechanical long travel release
Direction of tightening	Right-hand tightening
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Type of product	Torque screwdriver

---

## Accessories

"TQ-Station" – storage station for torque screwdrivers	659964
--	--------