



## Cut knurling tool set, Shank size: 25mm



### Order data

Order number	290219 25
GTIN	4030741656910
Item class	29H

### Description

#### Version:

**Modular design: Can be used universally as right-hand or left-hand version.**

Carbide running sleeve for increased wear resistance.

Quick tool adjustment by using the adjustment spindle.

#### Content:

1 pc. each knurling tool No. 290200 and No. 290210: Size 25

1 pc. each knurl No. 290276 and No. 290281: Size 25×6/0.8; 25×6/1.0; 25×6/1.5

2 pc. each knurl No. 290261: Size 25×6/0.8; 25×6/1.0; 25×6/1.5

### Technical description

Cutting direction	left-hand and right-hand
for knurl profile	RBL45° 1×BR15°
for knurl profile	RBL30° 1×AA
for knurl profile	RBR45° 1×BL15°
for knurl profile	RAA 1×BL30°
for knurl profile	RBR30° 1×AA

for knurl profile	RBL30° 1×AA
for knurl profile	RGE30° 2×AA
for knurl profile	RGE45° BL/BR45°
Type of product	Self-centering knurling tool

## Accessories

Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/1,5 mm	290276 25X6/1,5
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/0,8 mm	290261 25X6/0,8
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/1,0 mm	290276 25X6/1,0
Cut knurling tooluniversal Shank size 25 mm	290210 25
Cut knurling tooluniversal Shank size 25 mm	290200 25
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/1,0 mm	290261 25X6/1,0
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/0,8 mm	290276 25X6/0,8
Knurl PM Knurl Ø d1 × knurl width w / pitch 25X6/1,5 mm	290261 25X6/1,5