

Garant
SNMG 150608, Grade: HB7020


Order data

Order number	251230 HB7020
GTIN	4045197764140
Item class	21G

Description

SNMG 150608 HB7020 Corner radius: 0.8 mm
 Grade: HB7020
 Chip breaker: SM
 Cutting depth a_p : 0.5 - 6 mm
 Feed f : 0.15 - 0.5 mm/rev.
 Cutting speed v_c main application: 120 - 350 m/min

Technical description

Cutting conditions	slightly interrupted
Cutting depth a_p	0.5 - 6 mm
Corner radius	0.8 mm
Grade	HB7020
Feed f	0.15 - 0.5 mm/rev.
Chip breaker	SM
Cutting speed v_c main application	120 - 350 m/min

Main application	P
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	SNMG 150608
Number of changes/inserts	8
Type of product	Indexable insert for turning