

**Tapper up to M10, Type: 720938****Order data**

Order number	075550 720938
GTIN	4014586881256
Item class	03F

Description**Version:**

- **Electronic speed control for responsive starting.**
- **Sustained power for reliable performance.**
- **Integral reversing gear and quick backing out.**
- **FEIN sensitive handle for non-fatiguing and safe working.**
- **Integral switch for ease of use.**

Mains adaptor 220V.

Supplied with:

Without drill chuck. With additional handle. A collet chuck (No. 075580 size 063012) or a jaw chuck (No. 075580 size 019009) is required for operation.

Technical description

maximum machine tap Ø in steel	M10
Manufacturer's designation	GWP 10
Toolholder	B12
maximum speed	0 - 450 min ⁻¹
maximum vibration to EN	< 2.5 m/s ²

Weight	1.6 kg
Power consumption	450 W
Power supply	Mains operated
Packaging	Carrying case
Type of product	Tap driver

Accessories

Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Li-ion battery HighPower Battery type, battery voltage FE18 V	073834 FE18
Thread tapping accessories Type 063012	075580 063012
Thread tapping accessories Type 019009	075580 019009
Thread tapping accessories Type 009013	075580 009013