

uvex

Lace-up boot, black/red uvex 1 x-tended support, S3, EU shoe size: 44



Order data

| | |
|--------------|---------------|
| Order number | 092124 44 |
| GTIN | 4031101578101 |
| Item class | 04V |

Description

Version:

Sporty, especially lightweight and flexible safety shoe. Suitable for wearers allergic to chromium. Width 11.

- **Micro-velour uppers.**
- **Distance Mesh lining material.**
- **100% metal-free uvex xenova® toecap.**
- **PU sole with TPU inserts with the best damping characteristics.**
- **Virtually seamless design to avoid pressure points.**
- **ESD security.**

Lace-up boot with soft padded collar and padded tongue.

Safety shoe with medial and lateral support for the foot, for optimum position in the shoe.

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Composite

Puncture resistance: Textile

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

| | |
|--------------------------------|--|
| Colour | black/red |
| Puncture resistance | Textile |
| Material of protective toe-cap | Composite |
| Protection class | S3 |
| EU shoe size | 44 |
| Standard | Inlay type-tested according to DGUV regulation 191 |
| Series | uvex 1 |
| Gender | Gentlemen's |
| electrostatic characteristic | EGB/ESD |
| Type of product | Safety boots |